

SAV 242.22

2 magnetic contact surfaces which are switched on and off together (large prism and opposite prism). Available individually (S) and in pairs (P). Wooden storage box SAV 539.02-HK2 (for S) and SAV 539.04-HK4 (for P) (surcharge applies).

PERMANENT MAGNETIC V BLOCKS

Individually and in pairs


APPLICATION

Positioning

DESIGN

TECHNICAL DATA

- Perpendicularity: 0.004 mm
- Parallelism: 0.004 mm
- Prism angle: 90°



mm -		daN daN daN			
ength Widt	h Height	Workpiece diameter	Rated holding force, prism	Rated holding force, surface	Weight
80 67	96	6 - 66	40	90	2.9
100 70	96	6 - 70	40	120	3.8
RDERING E	CAMPLE	SAV no length - indi			

SAV 242.25

PERMANENT MAGNETIC V BLOCKS With two magnetic chucking areas



APPLICATION

Positioning

DESIGN

2 magnetic contact surfaces which are switched on and off together (large prism and opposite prism). Measuring surface and prism hardened. Available individually (S) and in pairs (P). Wooden storage box SAV 539.04 - HK4 available (surcharge applies).

TECHNICAL DATA

- Perpendicularity 0.004 mm
- Parallelism: 0.004 mm
- Prism angle: 90°



